

Specification Sheet

Part Number: 166-90130



HelaGuard Non-Metallic IP65 Fitting, 90-Elbow, NPT Thread, 0.75" Dia, PA66, Black, 10/pkg

Article Number

166-90130

Type

PSR075-90-0750

Color

Black (BK)

Features & Benefits

- External NPT thread provides a secure connection.
- Twist-on installation makes future access fast and easy.
- Internal spigot design helps ease threading of fitting onto conduit.
- All-around "teeth" attach firmly to conduit and deliver a high extraction force.
- Durable nylon material has high resistance to salts, oils, weak acids and solvents.
- IP65 rating for protection against wind, dirt and low pressure jets of water from all directions.

Quantity Per

bag

Product Description

Compression fittings feature a twist-on design for easy installation and future access. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Fits HelaGuard non-metallic conduits and tubing.

Short Description

HelaGuard Non-Metallic IP65 Fitting, 90-Elbow, NPT Thread, 0.75" Dia, PA66, Black, 10/pkg

Global Part Name

PSR075-90-0750-PA66-BK

Length L (Imperial)

2.48

Length L (Metric)

63

Variant

90° Elbow

Outside Diameter OD(Imperial)

1.65

Outside Diameter OD(metric)

42

Nominal Diameter (Imperial)

3/4

Nominal Diameter (Metric)

25

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Flammability

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +248°F (-40°C to +120°C)

Reach Complaint(Article 33)

Yes

| | |
|--------------------------------------|------------|
| ROHS Complaint | Yes |
| UL Recognized (US) | Yes |
| UL Recognized (US and Canada) | Yes |
| Package Quantity(Imperial) | 10 |
| Package Quantity (Metric) | 10 |
| Customs Number | 3926909988 |