

Specification Sheet

Part Number: 166-90195



HelaGuard Non-Metallic Conduit, Std. Weight, 1.50" Dia, Nylon PA6, Black, 50 ft/std reel

Article Number	166-90195
Type	HG-SW1500
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Material is easy to use and cut; reduces installation time and labor costs.• Flexible, abrasion resistant and durable for a variety of applications.• Good impact strength; recovers quickly if crushed.• UV resistant; suitable for use in outdoor applications.• Offered in fine or course corrugated pitch.
Quantity Per	reel

Product Description

A standard weight corrugated conduit made of PA6 nylon that offers flexible abrasion protection for wire and cable bundles. Easy to cut and use, the material is highly resistant to solvents and oils. Combine with HelaGuard non-metallic fittings for IP66 rating or greater protection against water, wind and dirt.

Short Description	HelaGuard Non-Metallic Conduit, Std. Weight, 1.50" Dia, Nylon PA6, Black, 50 ft/std reel
Global Part Name	HG-SW1500-PA6-BK
Length L (Imperial)	50.0
Length L (Metric)	15.2
Inner Diameter D (Imperial)	1.86
Inner Diameter D (Metric)	47.2
Outside Diameter OD(Imperial)	2.15
Outside Diameter OD(metric)	54.5
Nominal Diameter (Imperial)	1-1/2
Nominal Diameter (Metric)	54
Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +248°F (-40°C to +120°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

UL Listed (US and Canada)

Yes

UL Listed (US)

Yes

Package Quantity(Imperial)

50

Package Quantity (Metric)

15.2

Customs Number

3926909988