

Specification Sheet

Part Number: 166-90306



HelaGuard Non-Metallic IP66 Fitting, Straight, 1-1/2" NPT Thread, 1.25" Dia, PA66, Black, 2/pkg

Article Number	166-90306
Type	HG125-S-1500
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•External NPT thread provides a secure connection.•Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.•All-around "teeth" attach firmly to conduit and deliver a high extraction force.•Durable nylon material has high resistance to salts, oils, weak acids and solvents.•IP66 fitting has one-piece construction.
Quantity Per	bag
Product Description	Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

Short Description	HelaGuard Non-Metallic IP66 Fitting, Straight, 1-1/2" NPT Thread, 1.25" Dia, PA66, Black, 2/pkg
Global Part Name	HG125-S-1500-PA66-BK
Length L (Imperial)	2.32
Length L (Metric)	59
Variant	Straight
Outside Diameter OD(Imperial)	2.48
Outside Diameter OD(metric)	63
Nominal Diameter (Imperial)	1.25
Nominal Diameter (Metric)	42
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-58°F to +275°F (-50°C to +135°C)
Reach Complaint(Article 33)	Yes

ROHS Complaint	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	2
Package Quantity (Metric)	2
Customs Number	3926909988