

Specification Sheet

Part Number: 166-90323



HelaGuard Non-Metallic IP68 Fitting, Straight, M20 Thread, 0.38" Dia, PA66, Black, 10/pkg

Article Number	166-90323
Type	HGL038-S-M20
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•External NPT thread provides a secure connection.•Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.•All-around "teeth" attach firmly to conduit and deliver a high extraction force.•Durable nylon material has high resistance to salts, oils, weak acids and solvents.•IP68 fitting has additional conduit seal for increased protection against wind, dirt, and water.
Quantity Per	bag

Product Description

Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids, and solvents. Designed for easy removal with a small screwdriver. IP68 ingress protection rated fittings.

Short Description	HelaGuard Non-Metallic IP68 Fitting, Straight, M20 Thread, 0.38" Dia, PA66, Black, 10/pkg
Global Part Name	HGL038-S-M20-PA66-BK
Length L (Imperial)	1.73
Length L (Metric)	44
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Operating Temperature (Metric)	-58°F to +275°F (-50°C to +135°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

