

Specification Sheet

Part Number: 166-90326



HelaGuard Non-Metallic IP66 Fitting, Straight, M25 Thread, 0.75" Dia, PA66, Black, 10/pkg

Article Number

166-90326

Type

HG075-S-M25

Color

Black (BK)

Features & Benefits

- External NPT thread provides a secure connection.
- Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.
- All-around "teeth" attach firmly to conduit and deliver a high extraction force.
- Durable nylon material has high resistance to salts, oils, weak acids and solvents.
- IP66 fitting has one-piece construction.

Quantity Per

bag

Product Description

Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

Short Description	HelaGuard Non-Metallic IP66 Fitting, Straight, M25 Thread, 0.75" Dia, PA66, Black, 10/pkg
Global Part Name	HG075-S-M25-PA66-BK
Length L (Imperial)	1.97
Length L (Metric)	50
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Operating Temperature (Metric)	-58°F to +275°F (-50°C to +135°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

