

Specification Sheet

Part Number: 166-90327



Article Number	166-90327
Type	HG100-S-M32
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•External NPT thread provides a secure connection.•Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.•All-around "teeth" attach firmly to conduit and deliver a high extraction force.•Durable nylon material has high resistance to salts, oils, weak acids and solvents.•IP66 fitting has one-piece construction.
Quantity Per	bag
Product Description	Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

Short Description	HelaGuard Non-Metallic IP66 Fitting, Straight, M32 Thread, 1.00" Dia, PA66, Black, 10/pkg
Global Part Name	HG100-S-M32-PA66-BK
Length L (Imperial)	2.09
Length L (Metric)	53
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Operating Temperature (Metric)	-58°F to +275°F (-50°C to +135°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

