

## Specification Sheet

Part Number: 166-90333



HelaGuard Non-Metallic IP66 Fitting, 90-Elbow, 1-1/2" NPT Thread, 1.25" Dia, PA66, Black, 2/pkg

Article Number	166-90333
Type	HG125-90-1500
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•External NPT thread provides a secure connection.</li><li>•Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.</li><li>•Elbow features a smooth, swept bore to ease cable installation.</li><li>•All-around "teeth" attach firmly to conduit and deliver a high extraction force.</li><li>•Durable nylon material has high resistance to salts, oils, weak acids and solvents.</li><li>•IP66 fitting has one-piece construction.</li></ul>
Quantity Per	bag

### Product Description

Elbow fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

<b>Short Description</b>	HelaGuard Non-Metallic IP66 Fitting, 90-Elbow, 1-1/2" NPT Thread, 1.25" Dia, PA66, Black, 2/pkg
<b>Global Part Name</b>	HG125-90-1500-PA66-BK
<b>Length L (Imperial)</b>	3.90
<b>Length L (Metric)</b>	99.06
<b>Variant</b>	90° Elbow
<b>Outside Diameter OD(Imperial)</b>	2.48
<b>Outside Diameter OD(metric)</b>	63
<b>Nominal Diameter (Imperial)</b>	1-1/4
<b>Nominal Diameter (Metric)</b>	42
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-58°F to +275°F (-50°C to +135°C)
<b>Reach Complaint(Article 33)</b>	Yes

<b>ROHS Complaint</b>	Yes
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity(Imperial)</b>	2
<b>Package Quantity (Metric)</b>	2
<b>Customs Number</b>	3926909988