

Specification Sheet

Part Number: 166-90362



Metallic IP68 Compression Fitting, Straight Brass Swivel, 1/2"NPT, 0.50" (20mm) Dia, NPB Metal, 10/pkg

Article Number

166-90362

Type

LPC050-S-050

Color

Metal (ML)

Features & Benefits

- External nickel-plated brass NPT thread provides a durable connection.
- Swivel feature allows fitting to rotate until tightened.
- Metal ferrule insert has shallow & longer scroll for stronger fit with LPC smooth bore PVC tubings.
- IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.

Quantity Per

pack

Product Description

Multi-part metallic straight compression style fitting for use with LPC non metallic PVC tubing. Suitable for NPT threaded entries or knocknuts as fitting rotates until tightened. A longer and shallower scroll allows quick assembly and more durable fit with smooth bore tubing. Provides IP68 and up to IP69 ingress protection.

Short Description	Metallic IP68 Compression Fitting, Straight Brass Swivel, 1/2"NPT, 0.50" (20mm) Dia,NPB Metal,10/pkg
Global Part Name	LPC050-S-050-NPB-ML
Length L (Imperial)	1.32
Length L (Metric)	33.5
Variant	Straight
Height H (Imperial)	1.14
Height H (Metric)	29.0
Nominal Diameter (Imperial)	1/2
Nominal Diameter (Metric)	20
Material	Nickel Plated Brass (NPB)
Material Shortcut	NPB
Halogen free	Yes
Operating Temperature (Metric)	-58°F to +275°F (-50°C to +135°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes

Package Quantity(Imperial)

1

Package Quantity (Metric)

10

Customs Number

7412200000