

Specification Sheet

Part Number: LTP32G-25M



HelaGuard Spiral Metallic Conduit, Flexible, 1.0" (32mm) Dia, GS/PVC, Gray, 82ft/Reel

Article Number	166-90390
Type	LTS1008-25M
Color	Gray (GY)
Features & Benefits	<ul style="list-style-type: none">• Flexible metallic conduit provides liquid-tight performance to IP66 + IP67 + IP68 + IP69 when used with LTP or LTPUL series fittings.• Helically wound (spiral) galvanized steel core with an interlocking design delivers high degree of compression strength and impact resistance.• Smooth PVC cover resists oil and grease and will not wrinkle when conduit is bent; also resistant to acids.• UV-resistant (black), suitable for outdoor use.• Manufactured to UL360 requirements.
Quantity Per	reel

Product Description

A flexible, liquid-tight galvanized steel conduit with a smooth oil resistant PVC coating. LTP series is a general purpose, non-UL rated liquid-tight conduit used in applications that require movement, vibration and bending. Use with LTP or LTPUL series metallic fittings for IP66 + IP67 + IP68 + IP69 ratings. Designed for applications where a UL listing or CSA certification is not required but where a need still exists for a flexible metal conduit to protect wires against impact and exposure to oils and chemicals. My be used in hazardous locations when accompanied with LTPUL or EXD metallic fittings.

Short Description

HelaGuard Spiral Metallic Conduit, Flexible, 1.0" (32mm) Dia, GS/PVC, Gray, 82ft/Reel

Global Part Name

LTS1008-25M-GS/PVC-GY

Technical Description

Manufacturer Reference Number: LTP32G-25M

Length L (Imperial)

82.0

Length L (Metric)

25.0

Diameter D (imperial)

1.04

Diameter D (metric)

26.5

Outside Diameter OD(Imperial)

1.30

Outside Diameter OD(metric)

33.1

Nominal Diameter (Imperial)

1

Nominal Diameter (Metric)

32.0

Material

Polyvinylchloride (PVC) Galvanised Steel (GS)

Material Shortcut

PVC GS

Flammability

Self-Extinguishing according to EN IEC 61386-1

Halogen free

No

Operating Temperature (Metric)

-4°F to +221°F (-20°C to +105°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

82

Package Quantity (Metric)

25.0

Customs Number

8307100000

Weight (Metric)

18.3

Weight (Imperial)

40.3