

Specification Sheet

Part Number: LTP16-E



HelaGuard Metallic Conduit End Cap Insert, 0.38" (16mm) Dia, NPB Metal, 10/pkg

Article Number	166-90439
Type	LTS038-EI
Color	Metal (ML)
Features & Benefits	<ul style="list-style-type: none">• Single part insert creates smooth entry/exit point for wire and cables.
Quantity Per	pack
Product Description	Nickel plated brass end cap insert creates a smooth bore exit, ensuring cables do not get damaged. Twist-in ferrule serves as grounding core for liquid tight metallic conduits. Use with LTP series metallic conduits.
Short Description	HelaGuard Metallic Conduit End Cap Insert, 0.38" (16mm) Dia, NPB Metal, 10/pkg
Global Part Name	LTS038-EI-NPB-ML

Technical Description

Manufacturer Reference Number: LTP16-E

Length L (Imperial)

0.65

Length L (Metric)

16.5

Variant

Endcap

Height H (Imperial)

0.79

Height H (Metric)

20.0

Nominal Diameter (Imperial)

3/8

Nominal Diameter (Metric)

16.0

Material

Nickel Plated Brass (NPB)

Material Shortcut

NPB

Operating Temperature (Metric)

-58°F to +275°F (-50°C to +135°C)

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)