

## Specification Sheet

Part Number: 166-90466



HelaGuard Non-Metallic IP66 Fitting, 90-Elbow, 2" NPT Thread, 2" Dia, PA66, Black, 2/pkg

Article Number	166-90466
Type	HG200-90-2000
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•External NPT thread provides a secure connection.</li><li>•Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.</li><li>•Elbow features a smooth, swept bore to ease cable installation.</li><li>•All-around "teeth" attach firmly to conduit and deliver a high extraction force.</li><li>•Durable nylon material has high resistance to salts, oils, weak acids and solvents.</li><li>•IP66 fitting has one-piece construction.</li></ul>
Quantity Per	pack

### Product Description

Elbow fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

**Short Description**

HelaGuard Non-Metallic IP66 Fitting, 90-Elbow, 2" NPT Thread, 2" Dia, PA66, Black, 2/pkg

**Global Part Name**

HG200-90-2000-PA66-BK

**Variant**

90° Elbow

**Nominal Diameter (Imperial)**

2-5/8

**Nominal Diameter (Metric)**

67

**Material**

Polyamide 6.6 (PA66)

**Material Shortcut**

PA66

**Flammability**

UL 94 V2

**Halogen free**

Yes

**Operating Temperature (Metric)**

-58°F to +275°F (-50°C to +135°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**UL Recognized (US)**

Yes

**UL Recognized (US and Canada)**

Yes

**Package Quantity(Imperial)**

2

**Package Quantity (Metric)**

2

**Customs Number**

3926909988