


## Specification Sheet

Part Number: LTP25-075-EXD



Hazardous Area Liquid-Tight Flexible Metallic Comp Fitting, Straight, 3/4" NPT Thread, 0.75" (25mm) Dia, Metal, 1/pkg

**Article Number**

166-90570

**Type**

LTP25-075-EXD

**Color**

Metal (ML)

**Features & Benefits**

- Group I and II approvals
- Multi-part straight compression fitting includes elastomer seal and two-part epoxy resin pack for flameproof barrier and ingress protection ratings to IP66 + IP67 + IP68 + IP69.
- Durable Nickel Plated Brass material provides high mechanical strength, ensures electrical continuity and corrosion resistance.
- Suitable for knockouts or NPT/Metric threaded entries as fitting rotates until tightened.
- Interchangeable with liquid tight metallic conduits in the LTP / LTPHC / LTPLFH / LTPPU / LTBRDP / LTBRDLFH series.
- Suitable for use in Zone 1, Zone 2, Zone 21 and Zone 22 hazardous areas.
- ATEX and IECEx EX d (Flameproof).
- ATEX and IECEx EX e (Increased Safety).
- ATEX and IECEx EX ta (Dust Ignition Protection).

**Quantity Per**

pack

**Product Description**

Flameproof straight gland with inner Compound Barrier offers high specification, high quality solution for EX d, EX e, and EX ta applications. ATEX and/or IEC approvals for Group I and Group II. For indoor or outdoor use applications in Zone 1, Zone 2, Zone 21 and Zone 22 Hazardous areas. Nickel plated brass compression style fitting suitable for knockouts and NPT or Metric threaded entries for IP66 + IP67 + IP68 + IP69 ingress ratings. Use with LTP / LTPHC / LTPPU / LTBRDP / LTBRDLFH / and LTPLFH metallic conduit.

**Short Description**

Hazardous Area Liquid-Tight Flexible Metallic Comp Fitting, Straight, 3/4" NPT Thread, 0.75" (25mm) Dia, Metal, 1/pkg

**Global Part Name**

LTP25-075-EXD-NPB/PA6-ML

**Technical Description**

Manufacturer Reference Number: LTP25-075-EXD

**Length L (Imperial)**

1.97

**Length L (Metric)**

50.0

**Variant**

Straight

**Height H (Imperial)**

1.38

**Height H (Metric)**

35.0

**Nominal Diameter (Imperial)**

3/4

**Nominal Diameter (Metric)**

25.0

**Material**

Polyamide 6 (PA6) Nickel Plated Brass (NPB)

**Material Shortcut**

NPB PA6

<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-76°F to +185°F (-60°C to +85°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	1
<b>Package Quantity (Metric)</b>	1
<b>Customs Number</b>	8547900030