

Specification Sheet

Part Number: FU20-M20-M



Article Number

166-90764

Type

FU20-M20-M

Color

Metal (ML)

Features & Benefits

- Nickel plated brass compression fitting used with FU-x series flexible metallic conduit.
- Two part fitting comprised of shell and body with external metric thread delivers IP40 ingress protection.
- Suitable for knockouts and secured with a metric threaded locknut.

Quantity Per

pack

Product Description

Two-part nickel plated brass straight fitting with fixed external metric thread. Fitting comprised of shell and body suitable for knockout entries. For use with FU-x flexible metal conduit.

Short Description

Metallic Compression Fitting, Fixed Straight, M20 Metric Thread, 1/2" (20mm) Dia, NPB Metal, 10/pkg

Global Part Name

FU20-M20-M-NPB-ML

Technical Description

Manufacturer Reference Number: FU20-M20-M

Length L (Imperial)

1.03

Length L (Metric)

26.3

Variant

Straight

Height H (Imperial)

0.94

Height H (Metric)

24.0

Nominal Diameter (Imperial)

1/2

Nominal Diameter (Metric)

20.0

Material

Nickel Plated Brass (NPB)

Material Shortcut

NPB

Halogen free

Yes

Operating Temperature (Metric)

-58°F to +572°F (-50°C to +300°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

Customs Number

7412200000