

## Specification Sheet

Part Number: FU25-M25-M



Metallic Compression Fitting, Fixed Straight, M25 Metric Thread, 3/4" (25mm) Dia, NPB Metal, 10/pkg

<b>Article Number</b>	166-90765
<b>Type</b>	FU25-M25-M
<b>Color</b>	Metal (ML)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Nickel plated brass compression fitting used with FU-x series flexible metallic conduit.</li><li>• Two part fitting comprised of shell and body with external metric thread delivers IP40 ingress protection.</li><li>• Suitable for knockouts and secured with a metric threaded locknut.</li></ul>
<b>Quantity Per</b>	pack
<b>Product Description</b>	Two-part nickel plated brass straight fitting with fixed external metric thread. Fitting comprised of shell and body suitable for knockout entries. For use with FU-x flexible metal conduit.
<b>Short Description</b>	Metallic Compression Fitting, Fixed Straight, M25 Metric Thread, 3/4" (25mm) Dia, NPB Metal, 10/pkg

**Global Part Name**

FU25-M25-M-NPB-ML

**Technical Description**

Manufacturer Reference Number: FU25-M25-M

**Length L (Imperial)**

1.16

**Length L (Metric)**

29.5

**Variant**

Straight

**Height H (Imperial)**

1.14

**Height H (Metric)**

29.0

**Nominal Diameter (Imperial)**

3/4

**Nominal Diameter (Metric)**

25.0

**Material**

Nickel Plated Brass (NPB)

**Material Shortcut**

NPB

**Halogen free**

Yes

**Operating Temperature (Metric)**

-58°F to +572°F (-50°C to +300°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

10

**Package Quantity (Metric)**

10

**Customs Number**

7412200000