

Specification Sheet

Part Number: FU32-M32-M



Metallic Compression Fitting, Fixed Straight, M32 Metric Thread, 1" (32mm) Dia, NPB Metal, 2/pkg

Article Number	166-90766
Type	FU32-M32-M
Color	Metal (ML)
Features & Benefits	<ul style="list-style-type: none">• Nickel plated brass compression fitting used with FU-x series flexible metallic conduit.• Two part fitting comprised of shell and body with external metric thread delivers IP40 ingress protection.• Suitable for knockouts and secured with a metric threaded locknut.
Quantity Per	pack
Product Description	Two-part nickel plated brass straight fitting with fixed external metric thread. Fitting comprised of shell and body suitable for knockout entries. For use with FU-x flexible metal conduit.
Short Description	Metallic Compression Fitting, Fixed Straight, M32 Metric Thread, 1" (32mm) Dia, NPB Metal, 2/pkg

Global Part Name

FU32-M32-M-NPB-ML

Technical Description

Manufacturer Reference Number: FU32-M32-M

Length L (Imperial)

1.46

Length L (Metric)

36.8

Variant

Straight

Height H (Imperial)

1.42

Height H (Metric)

36.0

Nominal Diameter (Imperial)

1

Nominal Diameter (Metric)

32.0

Material

Nickel Plated Brass (NPB)

Material Shortcut

NPB

Halogen free

Yes

Operating Temperature (Metric)

-58°F to +572°F (-50°C to +300°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

2

Package Quantity (Metric)

2