

Specification Sheet

Part Number: 166-90828



Integrated Sealing Technology creates a true, one-piece component that reduces installation time and provides error free installation. Nickel plated brass metric thread provides a secure connection even under dynamic conditions.

Swivel thread feature minimizes cable twisting and provides strain relief.

All-around "teeth" attach firmly to corrugated conduit and deliver a high extraction force.

Fittings deliver IP68 ingress protection against moisture and dirt.

HelaGuard NM 28mm IP68 Ultra Fitting, 90-Elbow Brass Swivel, Ext M32 Thread, NPB, PA66, Black, 10/pkg

Article Number 166-90828

Type HGU34-90M-M32B

Color Black (BK)

Quantity Per pack

Product Description Straight snap-on style fittings with nickel plated brass metric threaded fitting provides a true, one-piece component solution; seals are integrated into the fitting body. Durable nylon materials deliver high chemical resistance against salts, oils, weak acids and solvents. Designed for fast assembly and easy removal using a small screwdriver.

| | |
|------------------------------|---|
| Short Description | HelaGuard NM 28mm IP68 Ultra Fitting, 90-Elbow Brass Swivel, Ext M32 Thread, NPB, PA66, Black, 10/pkg |
| Global Part Name | HGU34-90M-M32B-NPB/PA66-BK |
| Length L (Imperial) | 3.11 |
| Length L (Metric) | 79 |
| Variant | 90° Elbow |
| Nominal Diameter (Imperial) | 1 |
| Nominal Diameter (Metric) | 34 |
| Material | Polyamide 6.6 (PA66) Nickel Plated Brass (NPB) |
| Material Shortcut | PA66 NPB |
| Halogen Free | Yes |
| UV Resistant (Yes/No) | No |
| Operating Temperature | -58°F to +275°F (-50°C to +135°C) |
| Reach Compliant (Article 33) | No |
| ROHS Compliant | Yes |

| | |
|-----------------------------|------------|
| Package Quantity (Imperial) | 10 |
| Package Quantity (Metric) | 10 |
| Customs Number | 7412200000 |

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)