

Specification Sheet

Part Number: FSU20-E



HelaGuard Metallic Conduit End Cap Insert, Flexible 0.50" (20mm) Dia, NPB Metal, 10/pkg

Article Number	166-90844
Type	FSU20-E
Color	Metal (ML)
Features & Benefits	<ul style="list-style-type: none">• Single-part insert creates smooth entry / exit point for wire and cables.
Quantity Per	pack
Product Description	Nickel-plated brass end cap insert creates a smooth bore exit, protecting cables from damage. Twist-in ferrule serves as grounding core for spiral-constructed metallic conduit. Use with FSU, LFHU, FPU, SSU and FU-X series metallic conduit.
Short Description	HelaGuard Metallic Conduit End Cap Insert, Flexible 0.50" (20mm) Dia, NPB Metal, 10/pkg

Global Part Name

FSU20-E-NPB-ML

Length L (Imperial)

0.91

Length L (Metric)

23.0

Height H (Imperial)

0.90

Height H (Metric)

22.9

Nominal Diameter (Imperial)

1/2

Nominal Diameter (Metric)

20

Material

Galvanised Steel (GS)

Material Shortcut

NPB

Operating Temperature (Metric)

-148°F to +572°F (-100°C to +300°C)

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

Customs Number

7415290000

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)