

Specification Sheet

Part Number: FSU25-E



HelaGuard Metallic Conduit End Cap Insert, Flexible 0.75" (25mm) Dia, NPB Metal, 10/pkg

Article Number	166-90845
Type	FSU25-E
Color	Metal (ML)
Features & Benefits	<ul style="list-style-type: none">• Single-part insert creates smooth entry / exit point for wire and cables.
Quantity Per	pack
Product Description	Nickel-plated brass end cap insert creates a smooth bore exit, protecting cables from damage. Twist-in ferrule serves as grounding core for spiral-constructed metallic conduit. Use with FSU, LFHU, FPU, SSU and FU-X series metallic conduit.
Short Description	HelaGuard Metallic Conduit End Cap Insert, Flexible 0.75" (25mm) Dia, NPB Metal, 10/pkg

Global Part Name

FSU25-E-NPB-ML

Length L (Imperial)

1.08

Length L (Metric)

27.4

Height H (Imperial)

1.13

Height H (Metric)

28.7

Nominal Diameter (Imperial)

3/4

Nominal Diameter (Metric)

25

Material

Galvanised Steel (GS)

Material Shortcut

NPB

Operating Temperature (Metric)

-148°F to +572°F (-100°C to +300°C)

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

