

## Specification Sheet

Part Number: 166-90908



HelaGuard Non-Metallic IP68 Fitting, 90-Elbow, M32 Thread, 1.00" Dia, PA66, Black, 10/pkg

Article Number	166-90908
Type	HGL100-90-M32
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•External NPT thread provides a secure connection.</li><li>•Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.</li><li>•Elbow features a smooth, swept bore to ease cable installation.</li><li>•All-around "teeth" attach firmly to conduit and deliver a high extraction force.</li><li>•Durable nylon material has high resistance to salts, oils, weak acids and solvents.</li><li>•IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.</li></ul>
Quantity Per	pack

### Product Description

Elbow fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP68 ingress protection rated fittings.

<b>Short Description</b>	HelaGuard Non-Metallic IP68 Fitting, 90-Elbow, M32 Thread, 1.00" Dia, PA66, Black, 10/pkg
<b>Global Part Name</b>	HGL100-90-M32-PA66-BK
<b>Length L (Imperial)</b>	2.95
<b>Length L (Metric)</b>	75
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Operating Temperature (Metric)</b>	-58°F to +275°F (-50°C to +135°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	10
<b>Package Quantity (Metric)</b>	10
<b>Customs Number</b>	3926909988

