

Specification Sheet

Part Number: CTN1140STD



Article Number	169-60005
Type	CTN1140
Color	Black with Gray Stripe (BKSTGY)
Features & Benefits	<ul style="list-style-type: none">• Durable tubing provides protection of wire harness from friction, vibration, fraying and puncture• Tubing protects cables and wires against automotive fluids, vibration wear• Weather resistant material provides protection against water, snow, ice, and the effects of heat, cold, and sunlight
Quantity Per	carton
Product Description	<p>HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.</p>

Short Description	Convoluted Tubing, Slit, 1.25" Dia, PA6, Black with Gray Stripe, 250 ft/carton
Global Part Name	CTN1140-PA6-BK
Technical Description	Convoluted Tubing, Slit, 1-1/4" Dia., PA6, Black w/Gray Stripe
Length L (Imperial)	250.0
Length L (Metric)	76.2
Inner Diameter D (Imperial)	1.257
Inner Diameter D (Metric)	31.93
Diameter D (imperial)	1.50
Diameter D (metric)	38.10
Outside Diameter OD(Imperial)	1.50
Outside Diameter OD(metric)	38.10
Nominal Diameter (Imperial)	1.25
Nominal Diameter (Metric)	31.75
Wall Thickness WT (Imperial)	.006
Wall Thickness WT (Metric)	0.152

Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Flammability	UL 94 HB
Halogen free	No
Operating Temperature (Metric)	-40°F to +300°F (-40°C to +149°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	250
Package Quantity (Metric)	76.20
Customs Number	3926909988