

Specification Sheet

Part Number: CTN340STD



Convoluted Tubing, Slit, .75" Dia, PA6, Black with Gray Stripe, 550 ft/carton

Article Number	169-60013
Type	CTN340
Color	Black with Gray Stripe (BKSTGY)
Features & Benefits	<ul style="list-style-type: none">• Durable tubing provides protection of wire harness from friction, vibration, fraying and puncture• Tubing protects cables and wires against automotive fluids, vibration wear• Weather resistant material provides protection against water, snow, ice, and the effects of heat, cold, and sunlight
Quantity Per	carton

Product Description

HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

Short Description

Convoluted Tubing, Slit, .75" Dia, PA6, Black with Gray Stripe, 550 ft/carton

Global Part Name

CTN340-PA6-BK

Technical Description

Convoluted Tubing, Slit, 3/4" Dia., PA6, Black w/Gray Stripe

Length L (Imperial)

500.0

Length L (Metric)

152.4

Inner Diameter D (Imperial)

0.759

Inner Diameter D (Metric)

19.28

Diameter D (imperial)

0.989

Diameter D (metric)

25.12

Outside Diameter OD(Imperial)

0.989

Outside Diameter OD(metric)

25.12

Nominal Diameter (Imperial)

0.75

Nominal Diameter (Metric)

19.05

Wall Thickness WT (Imperial)	.005
Wall Thickness WT (Metric)	0.127
Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Flammability	UL 94 HB
Halogen free	No
Operating Temperature (Metric)	-40°F to +300°F (-40°C to +149°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	550
Package Quantity (Metric)	167.60
Customs Number	3926909988

