

Specification Sheet

Part Number: CTP120



Convoluted Tubing, Slit, .5" Dia, PE, Black, 8500 ft/carton

Article Number

169-60506

Type

CTP120

Color

Black (BK)

Features & Benefits

- Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install
- Tubing provides full coverage where spiral wrap or other coverings may not be suitable
- In harsh applications the tubing can provide resistance to crushing, impact, and abrasion
- Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires

Quantity Per

carton

Product Description

HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

Short Description

Convoluted Tubing, Slit, .5" Dia, PE, Black, 8500 ft/carton

Global Part Name

CTP120-PE-BK

Technical Description

Convoluted Tubing, Slit, 1/2" Dia., PE, Black

Length L (Imperial)

8500.0

Length L (Metric)

2590.8

Inner Diameter D (Imperial)

0.516

Inner Diameter D (Metric)

13.11

Diameter D (imperial)

0.70

Diameter D (metric)

17.78

Outside Diameter OD(Imperial)

0.70

Outside Diameter OD(metric)

17.78

Nominal Diameter (Imperial)

0.5

Nominal Diameter (Metric)

12.70

Wall Thickness WT (Imperial)	.005
Wall Thickness WT (Metric)	0.127
Material	Polyethylene (PE)
Material Shortcut	PE
Flammability	UL 94 V2
Halogen free	No
Operating Temperature (Metric)	-40°F to +199°F (-40°C to +93°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	8500
Package Quantity (Metric)	2590.80
Customs Number	3926909988

