

Specification Sheet

Part Number: 170-03054



Braided Sleeving, Aluminum Laminated Fiberglass, .5" Dia, AL/GF, Silver, 250 ft/bulk reel

Article Number

170-03054

Type

BSHTTST12SRB

Color

Silver (SR)

Features & Benefits

- A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.
- Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.
- Cuts with ordinary scissors for fast, easy application.

Quantity Per

reel

Product Description

High Temperature Aluminum Laminated Fiberglass Sleeving is a tubular shaped product that combines the protection of bonded aluminum and fiberglass into a single solution that is able to reflect radiant heat away from the sensitive contents inside the tube.

| | |
|---------------------------------------|---|
| Short Description | Braided Sleeving, Aluminum Laminated Fiberglass, .5" Dia, AL/GF, Silver, 250 ft/bulk reel |
| Global Part Name | BSHTTST12SRB-AL/GF-ML |
| Length L (Imperial) | 250.0 |
| Length L (Metric) | 76.2 |
| Bundle Diameter Min (Imperial) | 0.1 |
| Bundle Diameter Min (Metric) | 2.54 |
| Bundle Diameter Max (Imperial) | 0.437 |
| Bundle Diameter Max (Metric) | 11.1 |
| Diameter D (imperial) | 0.5 |
| Diameter D (metric) | 12.7 |
| Nominal Diameter (Imperial) | 1/2 |
| Nominal Diameter (Metric) | 12.7 |
| Wall Thickness WT (Imperial) | 0.025 |
| Wall Thickness WT (Metric) | 0.64 |
| Material | Glass Fiber (GF) Aluminum (AL) |

Material Shortcut

GF AL

Flammability

Non-Flammable

Halogen free

Yes

Operating Temperature (Metric)

-76°F to +491°F (-60°C to +255°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

250

Package Quantity (Metric)

76.20

Customs Number

7019905050

Weight (Metric)

2.90

Weight (Imperial)

6.375