

Specification Sheet

Part Number: 170-03072



Braided Sleeving, Expandable, Flame Retardant, .25" Dia, PET, Gray, 200 ft/reel

Article Number	170-03072
Type	BSPFR148
Color	Gray (GY)
Features & Benefits	<ul style="list-style-type: none">• Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required.• Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.
Quantity Per	reel

Product Description

A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification.

Short Description	Braided Sleeving, Expandable, Flame Retardant, .25" Dia, PET, Gray, 200 ft/reel
Global Part Name	BSPFR148-PET-GY
Length L (Imperial)	200.0
Length L (Metric)	61.0
Bundle Diameter Min (Imperial)	0.125
Bundle Diameter Min (Metric)	3.2
Bundle Diameter Max (Imperial)	0.437
Bundle Diameter Max (Metric)	11.1
Diameter D (imperial)	0.25
Diameter D (metric)	6.4
Nominal Diameter (Imperial)	1/4
Nominal Diameter (Metric)	6.4
Material	Polyester (PET)
Material Shortcut	PET
Flammability	Mil-202 FMVSS 302 FAR 25 UL VW-1

Halogen free Yes

Operating Temperature (Metric) -94°F to +257°F (-70°C to +125°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Certification/Specification WEB UL 94 VW-1

UL Recognized (US) Yes

Package Quantity(Imperial) 200

Package Quantity (Metric) 60.96

Customs Number 5808100000

Weight (Metric) 0.22

Weight (Imperial) 0.48