

## Specification Sheet

Part Number: 170-03073



Braided Sleeving, Expandable, Flame Retardant, .5" Dia, PET, Gray, 100 ft/reel

<b>Article Number</b>	170-03073
<b>Type</b>	BSPFR128
<b>Color</b>	Gray (GY)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required.</li><li>• Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.</li></ul>
<b>Quantity Per</b>	reel
<b>Product Description</b>	A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification.
<b>Short Description</b>	Braided Sleeving, Expandable, Flame Retardant, .5" Dia, PET, Gray, 100 ft/reel

Global Part Name

BSPFR128-PET-GY

Length L (Imperial)

100.0

Length L (Metric)

30.48

Bundle Diameter Min (Imperial)

0.25

Bundle Diameter Min (Metric)

6.4

Bundle Diameter Max (Imperial)

0.75

Bundle Diameter Max (Metric)

19.1

Diameter D (imperial)

0.50

Diameter D (metric)

12.7

Nominal Diameter (Imperial)

1/2

Nominal Diameter (Metric)

12.7

Material

Polyester (PET)

Material Shortcut

PET

Flammability

UL VW-1 Mil-202 FMVSS 302 FAR 25

Halogen free

Yes

<b>Operating Temperature (Metric)</b>	-94°F to +257°F (-70°C to +125°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL 94 VW-1
<b>UL Recognized (US)</b>	Yes
<b>Package Quantity(Imperial)</b>	100
<b>Package Quantity (Metric)</b>	30.48
<b>Customs Number</b>	5808100000
<b>Weight (Metric)</b>	0.33
<b>Weight (Imperial)</b>	0.72