


Specification Sheet

Part Number: 170-03087



Braided Sleeving, Split Wrap, 1.5" Dia, PET, Orange, 75 ft/bulk reel

Article Number

170-03087

Type

BSPSW1123B

Color

Orange (OG)

Features & Benefits

- Split wrap design needs no fasteners and installs quickly, saving assembly time and future accessibility without disassembly.
- Bends to a tight radius without distortion or splitting open.
- Unique construction retains shape and rigidity throughout unrolling.
- Easy open design allows quick access and ability to apply protective sleeving post assembly or post installation situations.

Quantity Per

reel

Product Description

A lateral split, semi-rigid and flame retardant braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.

Short Description	Braided Sleeving, Split Wrap, 1.5" Dia, PET, Orange, 75 ft/bulk reel
Global Part Name	BSPSW1123B-PET-OG
Length L (Imperial)	75.0
Length L (Metric)	22.9
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.54
Bundle Diameter Max (Imperial)	1.5
Bundle Diameter Max (Metric)	38.1
Diameter D (imperial)	2.0
Diameter D (metric)	50.8
Nominal Diameter (Imperial)	1-1/2
Nominal Diameter (Metric)	38.1
Wall Thickness WT (Imperial)	0.038
Wall Thickness WT (Metric)	0.97
Material	Polyester (PET)

Material Shortcut

PET

Flammability

UL 94 V0

Halogen free

Yes

Operating Temperature (Metric)

-94°F to +257°F (-70°C to +125°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

UL Recognized (US)

Yes

Package Quantity(Imperial)

75

Package Quantity (Metric)

22.86

Customs Number

5808100000

Weight (Metric)

0.95

Weight (Imperial)

2.1