

Specification Sheet

Part Number: 170-03124



Braided Sleeving, Split Wrap, .125" Dia, PET, Black, 400 ft/bulk reel

Article Number

170-03124

Type

BSPSW180B

Color

Black (BK)

Features & Benefits

- Center-slit overlapping design allows quick and easy access to the wires and cables for future maintenance or inspection without disassembly.
- Flexible material allows it to easily wrap around a variety of component shapes and sizes, making it easier to use than slit-loom tubing or spiral-wrap materials.
- A unique weave pattern provides increased coverage and greater resistance to abrasion, dust and debris.
- Overlapping design enhances flexibility, allowing it to shift and bend without exposing wire and cables.

Quantity Per

reel

Product Description

Split Wrap Woven Sleeving is a self-closing sleeving manufactured from a unique blend of monofilament and multifilament polyester fibers that resemble a tightly woven material. The wrap around design provides increased flexibility, better coverage and greater resistance from abrasion for wires, cables and assemblies. Can also be used to reduce noise in applications that involve movement, while protecting sensitive electronics and communication systems from dust and debris.

Short Description

Braided Sleeving, Split Wrap, .125" Dia, PET, Black, 400 ft/bulk reel

Global Part Name

BSPSW180B-PET-BK

Length L (Imperial)

400.0

Length L (Metric)

121.9

Bundle Diameter Min (Imperial)

0.1

Bundle Diameter Min (Metric)

2.54

Bundle Diameter Max (Imperial)

0.13

Bundle Diameter Max (Metric)

3.2

Diameter D (imperial)

0.13

Diameter D (metric)

3.0

Nominal Diameter (Imperial)

1/8

Nominal Diameter (Metric)

3.2

Wall Thickness WT (Imperial)

0.024

Wall Thickness WT (Metric)

0.61

Material	Polyester (PET)
Material Shortcut	PET
Flammability	UL 94 V0
Halogen free	Yes
Operating Temperature (Metric)	-94°F to +257°F (-70°C to +125°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
UL Recognized (US)	Yes
Package Quantity(Imperial)	400
Package Quantity (Metric)	121.92
Customs Number	5808100000
Weight (Metric)	0.36
Weight (Imperial)	0.8

