

## Specification Sheet

Part Number: 170-03147



Braided Sleeving, Split Wrap, Flame Retardant, 2" Dia, PET, Black, 50 ft/bulk reel

**Article Number**

170-03147

**Type**

BSSWFR200B

**Color**

Black (BK)

**Features & Benefits**

- Split wrap design installs quickly, saving assembly time and future accessibility without disassembly.
- Unique construction retains shape and rigidity throughout operating temperature range.
- Easy open design allows quick assembly, future access, and ability to apply protective sleeving post assembly or post installation situations.
- Self wrapping design eliminates the need for fasteners.
- Provides a greater flexibility than spiralwrap or convoluted tubing.

**Quantity Per**

box

**Product Description**

Used when flame retardancy is a primary requirement, this protection option incorporates a lateral split which allows the tube to open up to accommodate a variety of bundling requirements. The semi-rigid braid configuration simply closes around the entire installation without the need for any additional fasteners. Split wrap flame retardant braided sleeving is self-extinguishing and complies with UL VW-1 standards where cables exit a wall and need to be managed for an uncluttered, clean appearance.

**Short Description**

Braided Sleeving, Split Wrap, Flame Retardant, 2" Dia, PET, Black, 50 ft/bulk reel

**Global Part Name**

BSSWFR200B-PET-BK

**Length L (Imperial)**

50.0

**Length L (Metric)**

15.2

**Bundle Diameter Min (Imperial)**

0.1

**Bundle Diameter Min (Metric)**

2.54

**Bundle Diameter Max (Imperial)**

2.0

**Bundle Diameter Max (Metric)**

50.8

**Diameter D (imperial)**

2.0

**Diameter D (metric)**

50.8

**Nominal Diameter (Imperial)**

2

**Nominal Diameter (Metric)**

50.8

**Wall Thickness WT (Imperial)**

0.038

**Wall Thickness WT (Metric)** 0.97

**Material** Polyester (PET)

**Material Shortcut** PET

**Flammability** FAR 25 UL VW-1

**Halogen free** Yes

**Operating Temperature (Metric)** -94°F to +257°F (-70°C to +125°C)

**Reach Complaint(Article 33)** Yes

**ROHS Complaint** Yes

**UL Recognized (US)** Yes

**Package Quantity(Imperial)** 50

**Package Quantity (Metric)** 15.24

**Customs Number** 5808100000

**Weight (Metric)** 0.82

**Weight (Imperial)** 1.8

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)