

Specification Sheet

Part Number: 170-03151



Braided Sleeving, Hook & Loop, 2.0" Dia, PET, Black, 100 ft/bulk reel

Article Number

170-03151

Type

BSHKLP200B

Color

Black (BK)

Features & Benefits

- Flexible construction that conforms to irregular shapes and contours.
- Hook and loop feature wraps over cable bundle allowing future access to cables.
- Easy access saves assembly time and allows for easy splicing or insertion of additional wires.
- PET yarn construction offers excellent protection against cuts and abrasions.

Quantity Per

reel

Product Description

Designed for the quick and easy management of wires, this expandable sleeving has an internal hook and loop strap that is able to adhere to its outer PET braid, delivering flexibility that allows it to fit around odd-shaped connectors. Its color-matched hook and loop closure provides for an easy on and off installation, as well as instant and convenient access for harness break-outs and networks. The primary application for this sleeving is the wrapping and bunching of cables in a deployed situation or when frequent access to cables is necessary.

Short Description	Braided Sleeving, Hook & Loop, 2.0" Dia, PET, Black, 100 ft/bulk reel
Global Part Name	BSHKLP200B-PET-BK
Length L (Imperial)	100.0
Length L (Metric)	30.48
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.54
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.8
Diameter D (imperial)	2.0
Diameter D (metric)	50.8
Nominal Diameter (Imperial)	2
Nominal Diameter (Metric)	50.8
Wall Thickness WT (Imperial)	0.025
Wall Thickness WT (Metric)	0.635
Material	Polyester (PET)

Material Shortcut

PET

Flammability

FAR 25 UL 94 V0

Halogen free

Yes

Operating Temperature (Metric)

-94°F to +257°F (-70°C to +125°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

UL Recognized (US)

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

30.48

Customs Number

5808100000

Weight (Metric)

1.5

Weight (Imperial)

3.2