

Specification Sheet

Part Number: 170-03157



Braided Sleeving, Hook & Loop, Flame Retardant, 2.5" Dia, PET, Black, 100 ft/bulk reel

Article Number

170-03157

Type

BSHKLPFR212B

Color

Black (BK)

Features & Benefits

- Flexible construction that conforms to irregular shapes and contours.
- Hook and loop feature wraps over cable bundle allowing future access to cables.
- Easy access saves assembly time and allows for easy splicing or insertion of additional wires.
- Meets military specifications (Mil-202 approved.)
- Cuts easily with a benchmount hot knife.
- Resists chemicals and cleaning solvents.

Quantity Per

reel

Product Description

Flame retardant expandable braided sleeving with hook and loop strip for wrapping around cable assemblies. Color matched hook and loop closure provides an easy on and off installation, as well as convenient access for harness break-outs and when maintenance is necessary. Material is self-extinguishing and complies with UL VW-1 standards.

Short Description

Braided Sleeving, Hook & Loop, Flame Retardant, 2.5" Dia, PET, Black, 100 ft/bulk reel

Global Part Name

BSHKLPFR212B-PET-BK

Length L (Imperial)

100.0

Length L (Metric)

30.48

Bundle Diameter Min (Imperial)

0.1

Bundle Diameter Min (Metric)

2.54

Bundle Diameter Max (Imperial)

2.5

Bundle Diameter Max (Metric)

63.5

Diameter D (imperial)

2.50

Diameter D (metric)

63.5

Nominal Diameter (Imperial)

2-1/2

Nominal Diameter (Metric)

63.5

Wall Thickness WT (Imperial)

0.025

Wall Thickness WT (Metric)

0.635

Material

Polyester (PET)

Material Shortcut

PET

US MIL SPEC

MIL-STD-202

Flammability

UL VW-1

Halogen free

Yes

Operating Temperature (Metric)

-94°F to +257°F (-70°C to +125°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Certification/Specification WEB

UL MIL-STD 202

UL Recognized (US)

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

30.48

Customs Number

5808100000

Weight (Metric)

1.70

Weight (Imperial)

3.75

