

Specification Sheet

Part Number: 170-03186



Braided Sleeving, Split Wrap, 1.5" Dia, PET, Black, 50 ft/bulk reel

Article Number

170-03186

Type

BSSWV1120B

Color

Black (BK)

Features & Benefits

- Split wrap design needs no fasteners and installs quickly, saving assembly time and future accessibility without disassembly.
- Bends to a tight radius without distortion or splitting open.
- Unique construction retains shape and rigidity throughout unrolling.
- Easy open design allows quick access and ability to apply protective sleeving post assembly or post installation situations.

Quantity Per

reel

Product Description

A lateral split, semi-rigid and flame retardant braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires. More flexible than spiral wraps or convoluted tubing, this product is a fast and easy option for adding protection in post-assembly or post-installation applications.

Short Description

Braided Sleeving, Split Wrap, 1.5" Dia, PET, Black, 50 ft/bulk reel

Global Part Name

BSSWV1120B-PET-BK

Length L (Imperial)

50.0

Length L (Metric)

15.2

Bundle Diameter Min (Imperial)

0.1

Bundle Diameter Min (Metric)

2.54

Bundle Diameter Max (Imperial)

1.5

Bundle Diameter Max (Metric)

38.1

Diameter D (imperial)

1.50

Diameter D (metric)

38.1

Nominal Diameter (Imperial)

1-1/2

Nominal Diameter (Metric)

38.1

Wall Thickness WT (Imperial)

0.027

Wall Thickness WT (Metric)

0.68

Material

Polyester (PET)

Material Shortcut

PET

Flammability

UL 94 V0

Halogen free

Yes

Operating Temperature (Metric)

-94°F to +257°F (-70°C to +125°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

UL Recognized (US)

Yes

Package Quantity(Imperial)

50

Package Quantity (Metric)

15.24

Customs Number

5806322000

Weight (Metric)

1.02

Weight (Imperial)

2.25