

Specification Sheet

Part Number: 170-03192



Braided Wrap, Aluminum Laminated Fiberglass, 4' Long Stick, .5" Dia, AL/GF, Silver, 25/box

Article Number	170-03192
Type	BSHTTSW12SB
Color	Silver (SR)
Features & Benefits	<ul style="list-style-type: none">•A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.•Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.•Cuts with ordinary scissors for fast, easy application.
Quantity Per	box
Product Description	Aluminum Laminated Fiberglass Wrap sleeving combines the protection of bonded aluminum and fiberglass into a robust solution that deflects radiant heat away from sensitive wires and cables. Wrap-around design allows for fast and easy installation and maintenance. Sold in 4-foot sticks.

Short Description

Braided Wrap, Aluminum Laminated Fiberglass, 4' Long Stick, .5" Dia, AL/GF, Silver, 25/box

Global Part Name

BSHTTSW12SB-GF-AL-ML

Length L (Imperial)

4.0

Length L (Metric)

1.22

Bundle Diameter Min (Imperial)

0.1

Bundle Diameter Min (Metric)

2.54

Bundle Diameter Max (Imperial)

0.45

Bundle Diameter Max (Metric)

11.4

Diameter D (imperial)

0.5

Diameter D (metric)

12.7

Nominal Diameter (Imperial)

1/2

Nominal Diameter (Metric)

12.70

Wall Thickness WT (Imperial)

0.042

Wall Thickness WT (Metric)

1.06

Material

Glass fiber with aluminium foil (GF-AL)

Material Shortcut

GF-AL

Flammability

Non-Flammable

Halogen free

Yes

Operating Temperature (Metric)

-76°F to +491°F (-60°C to +255°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

25

Package Quantity (Metric)

25

Customs Number

7019905050