

## Specification Sheet

Part Number: 170-03198



Braided Wrap, Aluminum Laminated Fiberglass, 4' Long Stick, 2" Dia, AL/GF, Silver, 2/box

<b>Article Number</b>	170-03198
<b>Type</b>	BSHTTSW2SB
<b>Color</b>	Silver (SR)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.</li><li>•Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.</li><li>•Cuts with ordinary scissors for fast, easy application.</li></ul>
<b>Quantity Per</b>	box
<b>Product Description</b>	Aluminum Laminated Fiberglass Wrap sleeving combines the protection of bonded aluminum and fiberglass into a robust solution that deflects radiant heat away from sensitive wires and cables. Wrap-around design allows for fast and easy installation and maintenance. Sold in 4-foot sticks.

**Short Description**

Braided Wrap, Aluminum Laminated Fiberglass, 4' Long Stick, 2" Dia, AL/GF, Silver, 2/box

**Global Part Name**

BSHTTSW2SB-GF-AL-ML

**Length L (Imperial)**

4.0

**Length L (Metric)**

1.22

**Bundle Diameter Min (Imperial)**

0.1

**Bundle Diameter Min (Metric)**

2.54

**Bundle Diameter Max (Imperial)**

1.95

**Bundle Diameter Max (Metric)**

49.5

**Diameter D (imperial)**

2.0

**Diameter D (metric)**

50.80

**Nominal Diameter (Imperial)**

2

**Nominal Diameter (Metric)**

50.8

**Wall Thickness WT (Imperial)**

0.042

**Wall Thickness WT (Metric)**

1.06

**Material**

Glass fiber with aluminium foil (GF-AL)

**Material Shortcut**

GF-AL

**Flammability**

Non-Flammable

**Halogen free**

Yes

**Operating Temperature (Metric)**

-76°F to +491°F (-60°C to +255°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

2

**Package Quantity (Metric)**

2

**Customs Number**

7019905050