

Specification Sheet

Part Number: 170-22000



Helagaine Braided Sleeving, 20 mm Dia, PA66, GY, 164ft/Reel

Article Number

170-22000

Type

HEGPA6620

Color

Gray (GY)

Features & Benefits

- Nylon monofilament construction weave offers a tight braid that provides full coverage but will not rot or retain moisture.
- Material performs well in wet applications and where abiding substrate has a smooth surface.

Quantity Per

metre

Product Description

Helagaine Nylon Polyamide Expandable Braided Sleeving is a pliable yet durable sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion.

Short Description

Helagaine Braided Sleeving, 20 mm Dia, PA66, GY, 164ft/Reel

Global Part Name

HEGPA6620-PA66-GY

Length L (Imperial)	164.0
Length L (Metric)	50.0
Bundle Diameter Min (Imperial)	0.59
Bundle Diameter Min (Metric)	15
Bundle Diameter Max (Imperial)	0.91
Bundle Diameter Max (Metric)	23
Diameter D (imperial)	0.79
Diameter D (metric)	20.1
Nominal Diameter (Imperial)	3/4
Nominal Diameter (Metric)	20
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	FMVSS 302 UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-76°F to +302°F (-60°C to +150°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Certification/Specification WEB EN [45545-2]:2013

Package Quantity(Imperial) 164

Package Quantity (Metric) 50

Customs Number 5808100000

Content Unit(BMEcat) metre

Weight (Metric) 1.4

Weight (Imperial) 3.1