

## Specification Sheet

Part Number: 170-22500



Helagaine Braided Sleeving, 25 mm Dia, PA66, GY, 164ft/Reel

**Article Number**

170-22500

**Type**

HEGPA6625

**Color**

Gray (GY)

**Features & Benefits**

- Nylon monofilament construction weave offers a tight braid that provides full coverage but will not rot or retain moisture.
- Material performs well in wet applications and where abiding substrate has a smooth surface.

**Quantity Per**

metre

**Product Description**

Helagaine Nylon Polyamide Expandable Braided Sleeving is a pliable yet durable sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion.

**Short Description**

Helagaine Braided Sleeving, 25 mm Dia, PA66, GY, 164ft/Reel

**Global Part Name**

HEGPA6625-PA66-GY

<b>Length L (Imperial)</b>	164.0
<b>Length L (Metric)</b>	50.0
<b>Bundle Diameter Min (Imperial)</b>	0.71
<b>Bundle Diameter Min (Metric)</b>	18
<b>Bundle Diameter Max (Imperial)</b>	1.1
<b>Bundle Diameter Max (Metric)</b>	28
<b>Diameter D (imperial)</b>	0.98
<b>Diameter D (metric)</b>	24.9
<b>Nominal Diameter (Imperial)</b>	1
<b>Nominal Diameter (Metric)</b>	25
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	FMVSS 302 UL 94 V2
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-76°F to +302°F (-60°C to +150°C)

**Reach Complaint(Article 33)** Yes

**ROHS Complaint** Yes

**Certification/Specification WEB** EN [45545-2]:2013

**Package Quantity(Imperial)** 164

**Package Quantity (Metric)** 50

**Customs Number** 5808100000

**Content Unit(BMEcat)** metre

**Weight (Metric)** 1.8

**Weight (Imperial)** 3.9