

## Specification Sheet

Part Number: 181-00499



Solid Wall Wiring Duct, 2" x 1", Adhesive, PVC, Gray, 120ft/Carton

**Article Number**

181-00499

**Type**

SDA2X1

**Color**

Gray (GY)

**Features & Benefits**

- Solid wall construction provides excellent coverage to keep wires clean.
- Durable material protects wires from damage, with long-lasting performance.
- Standard colors complement or contrast light and dark environments.
- Nonpermanent adhesive allows repositioning prior to final installation.
- Optional covers snap on and off easily, and their nonslip lining ensures they stay in place even under vibration.

**Quantity Per**

carton

**Product Description**

HellermannTyton Solid Wall Duct efficiently routes and protects wire. It is designed for straight wire runs where break-outs are not required. Manufactured from high impact, rigid PVC, it comes in six-foot lengths. Pressure-sensitive, rubber-based adhesive backing aids in temporary positioning.

<b>Short Description</b>	Solid Wall Wiring Duct, 2" x 1", Adhesive, PVC, Gray, 120ft/Carton
<b>Global Part Name</b>	SDA2X1-PVC-GY
<b>Technical Description</b>	Adhesive
<b>Length L (Imperial)</b>	6.0
<b>Length L (Metric)</b>	1.83
<b>Width W (Imperial)</b>	2.0
<b>Width W (Metric)</b>	50.8
<b>Height H (Imperial)</b>	1.06
<b>Height H (Metric)</b>	26.9
<b>Mounting Hole Centers (Imperial)</b>	4.0
<b>Material</b>	Polyvinylchloride (PVC)
<b>Material Shortcut</b>	PVC
<b>Flammability</b>	Self-Extinguishing
<b>Halogen free</b>	No
<b>Operating Temperature (Metric)</b>	+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Certification/Specification WEB**

UL EN 50085-2-3\_1A EN 50085-1:2005 + A1:2013 CSA

**UL Recognized (US)**

Yes

**Package Quantity(Imperial)**

120

**Package Quantity (Metric)**

36.58

**Customs Number**

3925900000