

## Specification Sheet

Part Number: 181-00625



High Density Slotted Wall Wiring Duct, 1" X 3", Adhesive, PVC, Black, 120ft/Carton

**Article Number**

181-00625

**Type**

SLHDA1X3

**Color**

Black (BK)

**Features & Benefits**

- Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.
- Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.
- Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.

**Quantity Per**

carton

**Product Description**

Pro-Duct high density, slotted wall, wiring duct features narrow fingers, equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.

**Short Description**

High Density Slotted Wall Wiring Duct, 1" X 3", Adhesive, PVC, Black, 120ft/Carton

**Global Part Name**

SLHDA1X3-PVC-BK

**Technical Description**

Adhesive

**Length L (Imperial)**

6.0

**Length L (Metric)**

1.83

**Width W (Imperial)**

1.0

**Width W (Metric)**

25.4

**Height H (Imperial)**

3.07

**Height H (Metric)**

77.9

**Mounting Hole Centers (Imperial)**

2.0

**Material**

Polyvinylchloride (PVC)

**Material Shortcut**

PVC

**Flammability**

Self-Extinguishing

**Halogen free**

No

**Operating Temperature (Metric)**

+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Certification/Specification WEB**

EN 50085-1:2005 + A1:2013 UL EN 50085-2-3\_1A CSA

**UL Recognized (US)**

Yes

**Package Quantity(Imperial)**

120

**Package Quantity (Metric)**

36.58