

Specification Sheet

Part Number: 181-00642



High Density Slotted Wall Wiring Duct, 2" x 1", Adhesive, PVC, White, 120ft/Carton

Article Number	181-00642
Type	SLHDA2X1
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none">•Narrow fingers reduce fanning of wires to terminal blocks, providing a neater appearance.•Each finger features a double restriction to hold wires in the bottom portion of the duct, simplifying installation.•Mounting holes are uniform in size to those in slotted and solid wall duct but are provided every two inches to accommodate compact designs and provide ease of installation.•Nonpermanent adhesive allows repositioning prior to final installation.
Quantity Per	carton

Product Description

HellermannTyton High Density Slotted Wall Duct features narrow breakaway fingers, designed at a 2-to-1 ratio compared to standard slotted duct, providing additional access for wire leads. Narrower fingers better accommodate compact designs and components. Pressure-sensitive, rubber-based adhesive backing aids in temporary positioning.

Short Description

High Density Slotted Wall Wiring Duct, 2" x 1", Adhesive, PVC, White, 120ft/Carton

Global Part Name

SLHDA2X1-PVC-WH

Technical Description

Adhesive

Length L (Imperial)

6.0

Length L (Metric)

1.83

Width W (Imperial)

2.0

Width W (Metric)

50.8

Height H (Imperial)

1.06

Height H (Metric)

26.9

Mounting Hole Centers (Imperial)

2.0

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Flammability

Self-Extinguishing

Halogen free

No

Operating Temperature (Metric)

+122°F (+50°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Certification/Specification WEB

UL CSA EN 50085-1:2005 + A1:2013 EN 50085-2-3_1A

UL Recognized (US)

Yes

Package Quantity(Imperial)

120

Package Quantity (Metric)

36.58

Customs Number

3925900000