

Specification Sheet

Part Number: 181-00656



High Density Slotted Wall Wiring Duct, 3" x 3", Adhesive, PVC, Black, 120ft/Carton

Article Number

181-00656

Type

SLHDA3X3

Color

Black (BK)

Features & Benefits

- Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.
- Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.
- Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.

Quantity Per

carton

Product Description

Pro-Duct high density, slotted wall, wiring duct features narrow fingers, equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.

Short Description

High Density Slotted Wall Wiring Duct, 3" x 3", Adhesive, PVC, Black, 120ft/Carton

Global Part Name

SLHDA3X3-PVC-BK

Technical Description

Adhesive

Length L (Imperial)

6.0

Length L (Metric)

1.83

Width W (Imperial)

3.0

Width W (Metric)

76.2

Height H (Imperial)

3.07

Height H (Metric)

77.9

Mounting Hole Centers (Imperial)

2.0

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Flammability

Self-Extinguishing

Halogen free

No

Operating Temperature (Metric)

+122°F (+50°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Certification/Specification WEB

CSA EN 50085-1:2005 + A1:2013 EN 50085-2-3_1A UL

UL Recognized (US)

Yes

Package Quantity(Imperial)

120

Package Quantity (Metric)

36.58

Customs Number

3925900000