

## Specification Sheet

Part Number: 181-00659



High Density Slotted Wall Wiring Duct, 3" x 4", Adhesive, PVC, Gray, 120ft/Carton

<b>Article Number</b>	181-00659
<b>Type</b>	SLHDA3X4
<b>Color</b>	Gray (GY)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.</li><li>• Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.</li><li>• Mounting holes are uniform in size to the solid and slotted wall duct, but are offered every 2 inches to accommodate compact designs and ease installation.</li></ul>
<b>Quantity Per</b>	carton
<b>Product Description</b>	Pro-Duct high density, slotted wall, wiring duct features narrow fingers, equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.

**Short Description**

High Density Slotted Wall Wiring Duct, 3" x 4", Adhesive, PVC, Gray, 120ft/Carton

**Global Part Name**

SLHDA3X4-PVC-GY

**Technical Description**

Adhesive

**Length L (Imperial)**

6.0

**Length L (Metric)**

1.83

**Width W (Imperial)**

3.0

**Width W (Metric)**

76.2

**Height H (Imperial)**

4.07

**Height H (Metric)**

103.4

**Mounting Hole Centers (Imperial)**

2.0

**Material**

Polyvinylchloride (PVC)

**Material Shortcut**

PVC

**Flammability**

Self-Extinguishing

**Halogen free**

No

**Operating Temperature (Metric)**

+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Certification/Specification WEB**

CSA UL EN 50085-2-3\_1A EN 50085-1:2005 + A1:2013

**UL Recognized (US)**

Yes

**Package Quantity(Imperial)**

120

**Package Quantity (Metric)**

36.58

**Customs Number**

3925900000