

Specification Sheet

Part Number: 181-00676



High Density Slotted Wall Wiring Duct, 2" x 1", Adhesive, PVC, White, 30ft/Box

Article Number	181-00676
Type	SLHDA2X1
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none">•Narrow fingers reduce fanning of wires to terminal blocks, providing a neater appearance.•Each finger features a double restriction to hold wires in the bottom portion of the duct, simplifying installation.•Mounting holes are uniform in size to those in slotted and solid wall duct but are provided every two inches to accommodate compact designs and provide ease of installation.•Nonpermanent adhesive allows repositioning prior to final installation.
Quantity Per	box

Product Description

HellermannTyton High Density Slotted Wall Duct features narrow breakaway fingers, designed at a 2-to-1 ratio compared to standard slotted duct, providing additional access for wire leads. Narrower fingers better accommodate compact designs and components. Pressure-sensitive, rubber-based adhesive backing aids in temporary positioning.

Short Description	High Density Slotted Wall Wiring Duct, 2" x 1", Adhesive, PVC, White, 30ft/Box
Global Part Name	SLHDA2X1-PVC-WH
Technical Description	Adhesive
Length L (Imperial)	6.0
Length L (Metric)	1.83
Width W (Imperial)	2.0
Width W (Metric)	50.8
Height H (Imperial)	1.06
Height H (Metric)	26.9
Mounting Hole Centers (Imperial)	2.0
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	Self-Extinguishing
Halogen free	No
Operating Temperature (Metric)	+122°F (+50°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Certification/Specification WEB

UL EN 50085-2-3_1A EN 50085-1:2005 + A1:2013 CSA

UL Recognized (US)

Yes

Package Quantity(Imperial)

30

Package Quantity (Metric)

9.14

Customs Number

3925900000