

Specification Sheet

Part Number: 181-11503



Slotted Wall Wiring Duct, 1" x 1.5", Non-Adhesive, PVC, Gray, 30ft/Box

Article Number

181-11503

Type

SL1X1.5

Color

Gray (GY)

Features & Benefits

- Strong fingers prevent unwanted breaking.
- Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct.
- Restricted opening design in the finger of the duct helps keep wires in place.
- Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
- Supplied with mounting holes to streamline installation.
- Optional covers enhance protection and appearance.

Quantity Per

box

Product Description

Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts.

| | |
|---|--|
| Short Description | Slotted Wall Wiring Duct, 1" x 1.5", Non-Adhesive, PVC, Gray, 30ft/Box |
| Global Part Name | SL1X1.5-PVC-GY |
| Technical Description | Non-Adhesive |
| Length L (Imperial) | 6.0 |
| Length L (Metric) | 1.83 |
| Width W (Imperial) | 1.0 |
| Width W (Metric) | 25.4 |
| Height H (Imperial) | 1.57 |
| Height H (Metric) | 39.9 |
| Mounting Hole Centers (Imperial) | 4.0 |
| Material | Polyvinylchloride (PVC) |
| Material Shortcut | PVC |
| Flammability | Self-Extinguishing |
| Halogen free | No |
| Operating Temperature (Metric) | +122°F (+50°C) |

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Certification/Specification WEB

EN 50085-1:2005 + A1:2013 EN 50085-2-3_1A UL CSA

UL Recognized (US)

Yes

Package Quantity(Imperial)

30

Package Quantity (Metric)

9.14

Customs Number

3925900000