

Specification Sheet

Part Number: 181-12012



Article Number

181-12012

Type

SLA1X2

Color

White (WH)

Features & Benefits

- Strong fingers prevent unintended breaking.
- Fingers are easily deflected outward, allowing easier positioning of the wires.
- Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
- Nonpermanent adhesive allows repositioning prior to final installation.
- Optional covers snap on and off easily, and their nonslip lining ensures they stay in place even under vibration.

Quantity Per

box

Product Description

HellermannTyton Slotted Wall Duct features breakaway fingers that provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts. Pressure-sensitive, rubber-based adhesive backing aids in temporary positioning.

| | |
|---|---|
| Short Description | Slotted Wall Wiring Duct, 1" x 2", Adhesive, PVC, White, 30ft/box |
| Global Part Name | SLA1X2-PVC-WH |
| Technical Description | Adhesive |
| Length L (Imperial) | 6.0 |
| Length L (Metric) | 1.83 |
| Width W (Imperial) | 1.0 |
| Width W (Metric) | 25.4 |
| Height H (Imperial) | 2.07 |
| Height H (Metric) | 52.6 |
| Mounting Hole Centers (Imperial) | 4.0 |
| Material | Polyvinylchloride (PVC) |
| Material Shortcut | PVC |
| Flammability | Self-Extinguishing |
| Halogen free | No |
| Operating Temperature (Metric) | +122°F (+50°C) |

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Certification/Specification WEB

CSA EN 50085-1:2005 + A1:2013 UL EN 50085-2-3_1A

UL Recognized (US)

Yes

Package Quantity(Imperial)

30

Package Quantity (Metric)

9.14

Customs Number

3925900000