

Specification Sheet

Part Number: 181-15300



Solid Wall Wiring Duct, 1.5" x 3", Non-Adhesive, PVC, Gray, 120ft/Carton

Article Number	181-15300
Type	SD1.5X3
Color	Gray (GY)
Features & Benefits	<ul style="list-style-type: none">•Solid wall construction provides excellent coverage to keep wires clean.•Durable material protects wires from damage, with long-lasting performance.•Available standard colors complement or contrast in light and dark environments.•Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.
Quantity Per	carton
Product Description	HellermannTyton's Pro-Duct, Solid Wall wiring duct efficiently routes and protects wire. Solid Wall wiring duct it designed for straight wire runs where break outs are not required. Pro-Duct, Solid Wall wiring duct is manufactured from high impact, rigid PVC, comes in standard colors of white, gray and black, and is available in 6-foot lengths.

Short Description	Solid Wall Wiring Duct, 1.5" x 3", Non-Adhesive, PVC, Gray, 120ft/Carton
Global Part Name	SD1.5X3-PVC-GY
Technical Description	Non-Adhesive
Length L (Imperial)	6.0
Length L (Metric)	1.83
Width W (Imperial)	1.5
Width W (Metric)	38.1
Height H (Imperial)	3.07
Height H (Metric)	77.9
Mounting Hole Centers (Imperial)	4.0
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	Self-Extinguishing
Halogen free	No
Operating Temperature (Metric)	+122°F (+50°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Certification/Specification WEB

UL EN 50085-2-3_1A CSA EN 50085-1:2005 + A1:2013

UL Recognized (US)

Yes

Package Quantity(Imperial)

120

Package Quantity (Metric)

36.58

Customs Number

3925900000