

Specification Sheet

Part Number: SLWR30C2



Wire Retainer, Slotted Style for 3" Duct, Black, PA66, 100/Bag

Article Number	181-30031
Type	SLWR30
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Retainer spans approximately 90% over the duct opening for effective wire management.
Quantity Per	bag
Product Description	Slotted wall wire retainers snap in from the outside of the duct, allowing for fast and easy installation and removal. Slotted wall wire retainers are manufactured from black nylon 6/6.
Short Description	Wire Retainer, Slotted Style for 3" Duct, Black, PA66, 100/Bag
Global Part Name	SLWR30-PA66-BK

Technical Description

Wire Retainer, Slotted Style for 3" Duct

Length L (Metric)

1.83

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Flammability

UL 94 HB

Halogen free

Yes

Operating Temperature (Metric)

+23°F to +176°F (-5°C to +80°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988

