

## Specification Sheet

Part Number: 181-43002



Solid Wall Wiring Duct, 4" x 3", Non-Adhesive, PVC, White, 120ft/Carton

<b>Article Number</b>	181-43002
<b>Type</b>	SD4X3
<b>Color</b>	White (WH)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Solid wall construction provides excellent coverage to keep wires clean.</li><li>•Durable material protects wires from damage, with long-lasting performance.</li><li>•Available standard colors complement or contrast in light and dark environments.</li><li>•Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.</li></ul>
<b>Quantity Per</b>	carton

### Product Description

HellermannTyton's Pro-Duct, Solid Wall wiring duct efficiently routes and protects wire and cable. Solid Wall wiring duct is designed for straight wire runs where break outs are not required. Pro-Duct, Solid Wall wiring duct is manufactured from high impact, rigid PVC, comes in standard colors of white, gray and black, and is available in 6 foot lengths.

<b>Short Description</b>	Solid Wall Wiring Duct, 4" x 3", Non-Adhesive, PVC, White, 120ft/Carton
<b>Global Part Name</b>	SD4X3-PVC-WH
<b>Technical Description</b>	Non-Adhesive
<b>Length L (Imperial)</b>	6.0
<b>Length L (Metric)</b>	1.83
<b>Width W (Imperial)</b>	4.0
<b>Width W (Metric)</b>	101.6
<b>Height H (Imperial)</b>	3.07
<b>Height H (Metric)</b>	77.9
<b>Mounting Hole Centers (Imperial)</b>	4.0
<b>Material</b>	Polyvinylchloride (PVC)
<b>Material Shortcut</b>	PVC
<b>Flammability</b>	Self-Extinguishing
<b>Halogen free</b>	No
<b>Operating Temperature (Metric)</b>	+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Certification/Specification WEB**

UL EN 50085-2-3\_1A CSA EN 50085-1:2005 + A1:2013

**UL Recognized (US)**

Yes

**Package Quantity(Imperial)**

120

**Package Quantity (Metric)**

36.58

**Customs Number**

3925900000