


## Specification Sheet

Part Number: 181-44033



Slotted Wall Wiring Duct, 4" x 4", Adhesive, PVC, Gray, 120ft/Carton

**Article Number**

181-44033

**Type**

SLA4X4

**Color**

Gray (GY)

**Features & Benefits**

- Strong fingers prevent unintended breaking.
- Fingers are easily deflected outward, allowing easier positioning of the wires.
- Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
- Nonpermanent adhesive allows repositioning prior to final installation.
- Optional covers snap on and off easily, and their nonslip lining ensures they stay in place even under vibration.

**Quantity Per**

carton

**Product Description**

HellermannTyton Slotted Wall Duct features breakaway fingers that provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts. Pressure-sensitive, rubber-based adhesive backing aids in temporary positioning.

**Short Description**

Slotted Wall Wiring Duct, 4" x 4", Adhesive, PVC, Gray, 120ft/Carton

**Global Part Name**

SLA4X4-PVC-GY

**Technical Description**

Adhesive

**Length L (Imperial)**

6.0

**Length L (Metric)**

1.83

**Width W (Imperial)**

4.0

**Width W (Metric)**

101.6

**Height H (Imperial)**

4.07

**Height H (Metric)**

103.4

**Mounting Hole Centers (Imperial)**

4.0

**Material**

Polyvinylchloride (PVC)

**Material Shortcut**

PVC

**Flammability**

Self-Extinguishing

**Halogen free**

No

**Operating Temperature (Metric)**

+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Certification/Specification WEB**

EN 50085-2-3\_1A EN 50085-1:2005 + A1:2013 CSA UL

**UL Recognized (US)**

Yes

**Package Quantity(Imperial)**

120

**Package Quantity (Metric)**

36.58

**Customs Number**

3925900000