

## Specification Sheet

Part Number: 181-75750



Solid Wall Wiring Duct, .75" x .75", Non-Adhesive, PVC, Gray, 30ft/Box

**Article Number**

181-75750

**Type**

SD.75X.75

**Color**

Gray (GY)

**Features & Benefits**

- Solid wall construction provides excellent coverage to keep wires clean.
- Durable material protects wires from damage, with long-lasting performance.
- Available standard colors complement or contrast in light and dark environments.
- Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

**Quantity Per**

box

**Product Description**

HellermannTyton's Pro-Duct, Solid Wall wiring duct efficiently routes and protects wire. Solid Wall wiring duct it designed for straight wire runs where break outs are not required. Pro-Duct, Solid Wall wiring duct is manufactured from high impact, rigid PVC, comes in standard colors of white, gray and black, and is available in 6-foot lengths.

<b>Short Description</b>	Solid Wall Wiring Duct, .75" x .75", Non-Adhesive, PVC, Gray, 30ft/Box
<b>Global Part Name</b>	SD.75X.75-PVC-GY
<b>Technical Description</b>	Non-Adhesive
<b>Length L (Imperial)</b>	6.0
<b>Length L (Metric)</b>	1.83
<b>Width W (Imperial)</b>	0.75
<b>Width W (Metric)</b>	19.1
<b>Height H (Imperial)</b>	0.80
<b>Height H (Metric)</b>	20.3
<b>Mounting Hole Centers (Imperial)</b>	4.0
<b>Material</b>	Polyvinylchloride (PVC)
<b>Material Shortcut</b>	PVC
<b>Flammability</b>	Self-Extinguishing
<b>Halogen free</b>	No
<b>Operating Temperature (Metric)</b>	+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Certification/Specification WEB**

EN 50085-2-3\_1A EN 50085-1:2005 + A1:2013 UL CSA

**UL Recognized (US)**

Yes

**Package Quantity(Imperial)**

30

**Package Quantity (Metric)**

9.14

**Customs Number**

3925900000