

Specification Sheet

Part Number: 181-90051



Wiring Duct Cover for 1/2" Duct, 6 ft Long, PVC, Gray, 120 ft/carton

Article Number

181-90051

Type

TC.5

Color

Gray (GY)

Features & Benefits

- A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.
 - Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.
 - Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off.
- (Covers to be purchased separately)

Quantity Per

carton

Product Description

HellermannTyton's Pro-Duct wiring duct covers are sold separately and interchangeable among the 3 styles of duct (solid, slotted and high density). Manufactured from high impact, rigid PVC, Pro-Duct covers come in standard colors of white, gray and black. Wiring duct covers are available in 6 foot lengths.

| | |
|---------------------------------------|--|
| Short Description | Wiring Duct Cover for 1/2" Duct, 6 ft Long, PVC, Gray, 120 ft/carton |
| Global Part Name | TC.5-PVC-GY |
| Technical Description | Wiring Duct Cover for 1/2" Duct, Gray |
| Length L (Imperial) | 6.0 |
| Length L (Metric) | 1.83 |
| Width W (Imperial) | 0.64 |
| Width W (Metric) | 16.3 |
| Height H (Imperial) | 0.219 |
| Height H (Metric) | 5.56 |
| Material | Polyvinylchloride (PVC) |
| Material Shortcut | PVC |
| Flammability | Self-Extinguishing |
| Halogen free | No |
| Operating Temperature (Metric) | +122°F (+50°C) |
| Reach Complaint(Article 33) | No |

| | |
|--|--|
| ROHS Complaint | Yes |
| Certification/Specification WEB | UL CSA EN 50085-2-3_1A EN 50085-1:2005 + A1:2013 |
| UL Recognized (US) | Yes |
| Package Quantity(Imperial) | 120 |
| Package Quantity (Metric) | 36.58 |
| Customs Number | 3925900000 |