

Specification Sheet

Part Number: 181-91505



Wiring Duct Cover for 1-1/2" Duct, 6 ft Long, PVC, Intrinsic Blue, 120ft/carton

Article Number	181-91505
Type	TC1.5
Color	Blue (BU)
Features & Benefits	<ul style="list-style-type: none">•A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.•Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.•Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)
Quantity Per	carton

Product Description

HellermannTyton's Pro-Duct wiring duct covers are sold separately and interchangeable among the 3 styles of duct (solid, slotted and high density). Manufactured from high impact, rigid PVC, Pro-Duct covers come in standard colors of white, gray and black. Wiring duct covers are available in 6 foot lengths.

Short Description	Wiring Duct Cover for 1-1/2" Duct, 6 ft Long, PVC, Intrinsic Blue, 120ft/carton
Global Part Name	TC1.5-PVC-BU
Length L (Imperial)	6.0
Length L (Metric)	1.83
Width W (Imperial)	1.5
Width W (Metric)	38.1
Height H (Imperial)	0.308
Height H (Metric)	7.82
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	Self-Extinguishing
Halogen free	No
Operating Temperature (Metric)	+122°F (+50°C)
Reach Complaint(Article 33)	No
ROHS Complaint	Yes

Certification/Specification WEB

EN 50085-1:2005 + A1:2013 UL EN 50085-2-3_1A CSA

UL Recognized (US)

Yes

Package Quantity(Imperial)

120

Package Quantity (Metric)

36.58

Customs Number

3925900000